

The products are 100% recyclable

The world is our home.

Save our resources.



Waste Management Catalogue

special uses	containers	2 wheeled bins	4 wheeled bins	
	domestic collection and street furniture	municipal solid waste collection and municipal selective waste collection (according to UNI EN 840-1-5-6 and RAL -GZ 951/1)	municipal solid waste collection and municipal selective waste collection (according to UNI EN 840-2-3-4-5-6)	
from 300 to 600	10 25 40 50	80 120 140 240 360	660 770 1000 1000L reinforced 1100L flat lid 1100L round lid 1700	    <p>CE PRINTING and indication of sound power level according to 2000/14/EC directive on 80L, 120L, 140L, 240L, 360L, 660L, 770L, 1000L, 1100L flat lid and round lid</p> <p>The products are injection moulded in high density polyethylene (HDPE) therefore they are 100% recyclable</p> <p>The products 240L, 360L, 660L, 770L, 1100L are ONU ADR certified for the transport of clinical waste. The box 600L FOR SPECIAL USES IS ADR ONU certified for the transport of expired batteries.</p> <p>The products are certified GS-TÜV (Certificate of the product and the safety at work according to EN 840 standard, RAL-GZ 951/1 and EN 12574).</p>
				<p>reflective stripes class one and/or two</p> <p>generic stickers (one colour to four-colour print)</p> <p>progressive serial number printing</p> <p>embossing, hot foil stamping, silk screen printing</p> <p>in Mould Labelling</p> <p>personalized labels (barcodes, serial numbers..)</p> <p>chip allocation</p> <p>standard colours (special colours available on request)</p> <p>bag-holding lid</p> <p>wheels options (ø 200 mm standard)</p> <p>lid with rubber round aperture ø 90 mm for can waste collection</p> <p>lid with rubber round aperture ø 160 mm for glass/plastics waste collection</p> <p>lid with rubber round aperture ø 200 mm for glass/plastics waste collection</p> <p>lid with rubber round aperture ø 280 mm for glass/plastics waste collection</p> <p>lid with rectangular aperture and rubber protection (150x250 or 260x215)</p> <p>aperture for paper collection</p> <p>specific insert for expired medicines collection</p> <p>specific insert for expired batteries collection</p> <p>lid within lid insert</p> <p>micro-perforations allowing air to circulate for organic fraction</p> <p>grill fitted in the base of the container for organic fraction</p> <p>lock with triangular key</p> <p>SUDHAUS gravity lock or with triangular key</p> <p>JCO gravity lock</p> <p>directional lock</p> <p>halved lid (2 pieces)</p> <p>foot pedal for lid opening</p> <p>dampened closing lid</p> <p>central brake</p> <p>additional handles</p> <p>stationary model (with feet)</p> <p>Tow-hook</p> <p>male lifting device DIN+ EN 840 (other lifting systems available on request)</p> <p>Comb lifting device EN 840 C (DIN)</p> <p>Comb lifting device EN 840 A (AFNOR)</p> <p>Bologna lifting device/DIN fitted on Bologna lifting device</p> <p>male lifting device fitted on box device EN12574</p> <p>Diamond lifting device</p>
	 applicable	 applicability to be verified with the sales department	nb: the accessories and the personalizations of the above synoptic table are only a part of the optionals that can be required. Please contact our sales department for optionals that are not stated above.	

We reserves the right to alter the data of the described models due to technical or commercial modifications and improvements at any time without giving notice.

660

770

1000

standard models



reinforced

selective collection



other applications and options

foot pedal for lid opening



tow hook



back hinge and handle



foot pedal provided with shock-absorber



empty by upturning using forks



front side of a reinforced body



AFNOR comb (A-EN840)



AFNOR bar

foot pedal provided with shock-absorber



drain plug



flat lid



round lid

versions
standardselective
collection

detail of a foot pedal rod



child safety device



central brake



child safety device

other
applications
and
options

halved lid (2 pieces)



single lid application



stationary model with feet

lifting equipments: Bologna, DIN on Bologna device,
male on box device, Diamond



Aperture for paper collection (OUR REF.)	Container size	Aperture size (mm)
ARCL03	660/770 Lt. Flat lid	600 x 80
ARCL18	1000/1100 Lt. New flat lid (B) Large size	400 x 200
ARCL 19 / ARCL 20	660/770 (B) - 1000/1100 Lt. New flat lid (B)	600 x 160
ARCL01B	1000/1100 Lt. New Range (B)	610 x 80
ARCL01 / ARCL07	1100 Lt. Round lid	610 x 80 / 610 x 160
ARCL08	1700 Lt. Single lid	700 x 100



support feet with positioning
rollers



foot pedal opening for disposal
lid



side handle for all users
accessibility (optional)



reduced aperture



reinforced bottom with ribs equipped
with drain plugs for waste sewage discharge



steel lifting trunnions



patented centering system



ergonomic disposal lid



rounded edges

60



80



120



140



240




360



standard models

selective collections



wheel ø 200



nose wheel ø 300



handling support



handling handless



waste separation and recycling unit equipped with Safetyplast railings



patented spring system



bag-holding lid

foot pedal for lid opening

60•80•120•140•240•360



standard personalizations on request

standard colours

